



DG 700 L

- Particularly powerful and robust for demanding use
- For sanding/grinding, deburring, moulding/routing and engraving
- For grinding flat and curved surfaces in a variety of different materials
- Practical and lightweight for easy operation even in difficult to reach places
- Ergonomic, insulated and lightweight housing made from impact-proof plastic
- User-friendly exhaust guide through the handle avoids dust turbulence in the working area
- Sound-proofed air outlet for reduced noise operation
- Compact dimensions for convenient one-hand operation
- Long spindle for improved access to difficult to reach places

Order no.	601555000
EAN code	4007430245670

Operating pressure	6.2 bar / 90 psi
Air requirement	600 l/min / 21 cfm
Maximum speed	22000 rpm
Collet chuck bore	6 mm / 0.2362 "
Weight	1.3 kg / 2.9 lbs

Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", Collet 6 mm (industry standard), Oil bottles