



DW 125

- For grinding flat and curved surfaces in a variety of different materials
- Ergonomic, insulated and lightweight housing made from impact-proof plastic
- User-friendly exhaust guide through the handle avoids dust turbulence in the working area
- Sound-proofed air outlet for reduced noise operation
- Safety lever prevents unintentional start of the machine
- For use with roughing and separating discs Ø 125 mm
- Numerous grinding wheels and cutting discs are available in the Metabo range

Order no.	601556000
EAN code	4007430245687

Disc-Ø	125 mm / 5 "
Operating pressure	6.2 bar / 90 psi
Air requirement	500 l/min / 18 cfm
No-load speed	10000 rpm
Spindle thread	M 14
Weight	1.8 kg / 4 lbs

Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", Hexagonal wrench, Side handle, Flat-pin spanners, Protective cover for disc, Open-jawed spanner, Oil bottles