



## DSX 150

- Ergonomic, insulated and lightweight housing made from impact-proof plastic
- Compact dimensions for convenient one-hand operation
- For grinding flat and curved surfaces in a variety of different materials
- Infinitely variable speed control for working with different materials
- Sound-proofed air outlet for reduced noise operation
- Suitable for wet and dry sanding/grinding
- Separate exhaust: connection option Ø 25 mm to external dust extraction
- 6-hole backing pad Ø 150 mm with hook and loop for use of currently available sandpapers

<b>Order no.</b>	<b>601558000</b>
<b>EAN code</b>	<b>4007430245809</b>
Grinding plate Ø	150 mm / 6 "
Operating pressure	6.2 bar / 90 psi
Air requirement	550 l/min / 19 cfm
Working stroke	5 mm / 3/16 "
Speed (RPM)	12000 rpm
Weight	1 kg / 2.2 lbs

### Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", Open-jawed spanner, Hexagonal wrench, Oil bottles