



## DBF 457

- Powerful, compact band file for grinding, satin-finish and deburring in difficult to reach places
- Tool-less sanding belt exchange and automatic belt tensioning
- Grinding attachment can be swivelled through 360° for perfect adaptation to any working position
- User-friendly exhaust guide through the handle avoids dust turbulence in the working area
- Safety lever prevents unintentional start of the machine
- Suitable for sanding belts 13 x 457 mm.

Order no.	601559000
EAN code	4007430245816
Operating pressure	6.2 bar / 90 psi
Air requirement	400 l/min / 14 cfm
Grinding belt width	13 mm // 1/4 "
Grinding belt length	457 mm / 18 "
Belt speed in idle	20 m/s // 3937 ft/min
Useful length of sanding belt arm	90 mm / 3 9/16 "
Weight	1.5 kg / 3.3 lbs

### Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", Sanding belt (13 x 457mm;P120), Fleece band (13 x 457mm; medium), Hexagonal wrench, Oil bottles