



DKG 80/16

- For processing staples
- For fixing liners, materials, insulation material
- Practical and lightweight for easy operation even in difficult to reach places
- Ergonomic composite housing: insulated non-slip and low vibration for comfortable work
- Rubberised handle for ergonomic and fatigue-free operation

Order no.	601564500
EAN code	4007430245953
Staple type	80
Staple length	4 - 16 mm // 3/16 - 5/8 "
Operating pressure	5 - 7 bar // 72.5 - 101.5 psi
Air requirement per impact	0.34 l / 0.01 cfi
Weight	0.78 kg / 1.7 lbs

Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", Oil bottles, Safety Goggles, Plastic carry case