



## DSN 50

- For processing nails
- For interiors, e.g. for fixing wall and ceiling panels or for attaching strips
- Practical and lightweight for easy operation even in difficult to reach places
- Thumbwheel depth control for accurate working results
- Safety mechanism prevents unintentional trigger action for the protection of the user
- Tool-free opening of the front cover for simple and rapid elimination of faults
- Ergonomic composite housing: insulated non-slip and low vibration for comfortable work
- Rubberised handle for ergonomic and fatigue-free operation
- User-friendly, rotating exhaust guide: no dust turbulence in the working area

<b>Order no.</b>	<b>601568500</b>
<b>EAN code</b>	<b>4007430245991</b>

Nail type	SKN
Nail length	15 - 50 mm // 5/8 - 2 "
Operating pressure	5 - 8 bar // 72.5 - 116 psi
Air requirement per impact	0.66 l / 0.02 cfi
Weight	0.92 kg / 2 lbs

### Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", Oil bottles, Safety Goggles, Plastic carry case