



FSP 600 LVLP

- LVLP (Low Volume Low Pressure): min. working pressure 0.7 bar at the nozzle kit, transfer rate approximately 73%. Low overspray, maximum transfer efficiency with very low air consumption
- Infinitely adjustable for circular and wide spray
- Easy to clean, for the highest precision and service life
- Nozzle kit made from stainless steel, suitable for use with water-soluble materials and materials containing solvents

Order no.	601578000
EAN code	4007430246202

Operating pressure	1.6 bar / 23.2 psi
Air requirement	136 l/min // 5 cfm
Weight	0.7 kg / 1.5 lbs

Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", Plastic flow bowl, 0.6 l, Filter, Nozzle Ø 1.3 mm, Cleaning brush, Assembly key