



## Mega 350-50 W

- More powerful and robust V-belt compressor for demanding use
- Belt drive for low speeds and a particularly quiet operation
- Oil-lubricated Piston Condenser
- For single phase alternating current
- Operating pressure can be regulated according to application by means of a pressure reducer and manometer
- Convenient pressure switch for good cold starting, complete with relief valve
- Additional manometer for displaying the tank pressure
- Overload protection: protects the motor from overheating
- Rubberised, stable wheels and pull handle for mobile use
- 10 year tank warranty against rust

Order no.	60158900
EAN code	4007430272041
Suction rate	320 l/min / 85 gal/h
Filling capacity	250 l/min / 8.8 cfm
Effective delivery volume (at 80% max. pressure)	220 l/min / 7.8 cfm
Maximum pressure	10 bar / 145 psi
Mains voltage	220 - 240 V
Rated input power	2.2 kW / 3 HP
Maximum speed	1350 rpm
Tank capacity	50 l / 13.2 gal
Sound pressure level (LpA)	86 dB(A)
Sound power level (LwA)	93 dB(A)
Dimensions	880 x 490 x 780 mm // 2.9 x 1.6 x 2.6 ft
Weight	52 kg / 115 lbs
Cable length	1.5 m / 5 ft

### Scope of delivery

2 Universal couplings