



DSSW 500-1/2" C

- For tightening car wheel bolts, for assembly work and repairs. Universal use
- Practical and lightweight for easy operation even in difficult to reach places
- Ergonomic composite housing: insulated non-slip and low vibration for comfortable work
- Ergonomic forward/reverse switching with convenient one-hand operation
- User-friendly exhaust guide through the handle avoids dust turbulence in the working area
- Torque can be set at 4 levels for different tightening applications
- Durable twin hammer

Order no.	601590000
EAN code	4007430335388
Operating pressure	6.2 bar / 90 psi
Air requirement	7 l/s / 15 cfm
Square holder	1/2"
Maximum torque	540 Nm / 400 ft. lbs
Max. loosening torque	860 Nm / 630 ft. lbs
Weight	1.2 kg / 2.6 lbs

Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", Hose nozzle 10 mm and hose clamp according to ISO 11148, Oil bottles