



NIV 18 LTX BL 1.6

- Handy, powerful cordless nibblers for effortless cutting of flat and shaped sheets
- Good cornering ability for notches and interior cut-outs of a radius of 40 mm or more
- Fast, tool-free adjustment of cutting direction by up to 360°, in 45° steps
- High feed rate for faster working, thanks to an efficient brushless motor
- Infinitely adjustable cutting speed for individual customisation to the given material and task at hand
- Distortion- and spark-free cutting, without the annoyance of metal dust
- Comfortable handling thanks to low weight, slim grip area and switch located on the top
- Metabo Quick: tool-free quick changing of dies and punches
- Electronic overload protection for long service life
- With chip collection bag to protect against contact corrosion from ejected chips
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601614850
EAN code	4061792188938
Type of battery pack	Li-Power
Battery voltage	18 V
Max. sheet thickness for steel: 400 N/mm ²	1.6 mm / 0.0629 "
Max. sheet thickness for steel: 600 N/mm ²	1.2 mm / 0.0472 "
Max. sheet thickness for steel: 800 N/mm ²	0.7 mm / 0.0275 "
Max. sheet thickness for aluminium: 250 N/mm ²	2 mm / 0.0787 "
Strokes in idle	660 - 2360 rpm
Cutting speed	1.2 - 2.6 m/min // 47.2 - 102.3 inch/ min
Cutting width	5 mm / 0.1968 "
Starting hole diameter	21 mm / 0.8267 "
Smallest curve radius	40 mm / 1.5748 "
Weight without battery pack	1.3 kg / 2.9 lbs
Weight with battery pack	1.7 kg / 3.7 lbs

Scope of delivery

Punch, Die, Chip Collection Bag, Combo-spanner, without battery pack, without charger