



KH 18 LTX 24

- Cordless hammer with SDS plus holder for powerful hammer drilling and chiselling - any time and anywhere
- Dust-free drilling with external dust extraction ESA plus
- Combination hammer with 3 functions: hammer drilling, drilling and chiselling
- Variospeed (V) Electronics for working at customised speeds to suit various application materials
- Electronic soft start for precise spot-drilling
- Safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly
- With attachment point for tool safety straps for working at great heights
- LED work light for optimum view of the drilling site
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601712850
EAN code	4061792213197
Battery voltage	18 V
Max. single blow energy (EP-TA)	2.1 J
Maximum impact rate	5200 bpm
Drill-Ø concrete with hammer drills	24 mm / 1 "
Drill-Ø masonry with core bits	68 mm / 2 11/16 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	30 mm / 1 3/16 "
No-load speed	0 - 1400 rpm
Bit retainer	SDS-plus
Weight without battery pack	2.6 kg / 5.73 lbs

Scope of delivery

Side handle, Drilling depth guide, without battery pack, without charger