



KH 18 LTX BL 28 Q with Metabo Quick change chuck

- Extremely light and compact cordless hammer with integrated extraction interface
- Maximum drill performance, efficiency and service life thanks to brushless technology and high-performance hammer action
- Dust-free drilling with compact dust extraction ISA 28 (accessory)
- Combination hammer with 3 functions: hammer drilling, drilling and chiselling
- Metabo VibraTech (MVT): working, also continuously, in a low-fatigue manner whilst protecting the user's health
- Metabo Quick: fast, tool-free chuck for working with SDS-plus and straight shank drill bits
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics for work with materials requiring customised speeds, which remain constant under load
- Optional reduction of speed and impact energy for working in softer materials
- Electronic soft start for precise spot-drilling
- Double safety when the drill bit jams: No kick-back thanks to the mechanic decoupling plus ultra-fast sensor-controlled shutdown
- LED work light for optimum view of the drilling site
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601715840
EAN code	4061792218611
Battery voltage	18 V
Max. single blow energy (EP-TA)	3 J
Maximum impact rate	4470 bpm
Drill-Ø concrete with hammer drills	28 mm / 1 3/32 "
Drill-Ø masonry with core bits	82 mm / 3 7/32 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	30 mm / 1 3/16 "
No-load speed	0 - 1000 rpm
Bit retainer	SDS-plus
Weight without battery pack	3.4 kg / 7.5 lbs

Scope of delivery

Hammer chuck for tools with SDS-plus shank end, Keyless chuck for tools with cylindrical shank, rubber-coated side handle, Drilling depth guide, metaboX 165 L, without battery pack, without charger