



## HS 18 LTX 45

- Extremely light and quiet cordless hedge trimmer for effortless trimming of hedges and shrubs
- Clean cuts thanks to laser-cut, diamond-ground blades
- High cutting output thanks to special drop shape of the blade teeth: No escaping of the twigs while cutting
- Comfortable two-hand operation thanks to long trigger button with inside bow-type handle switch
- High user safety thanks to additional safety switch and blade quick stop (in 0.08 seconds)
- Comfortable working thanks to perfect balance, low-vibration operation and softgrip handle
- Trigger guard protects user and gearing when working near walls and the ground
- Space-saving storage at the wall by means of practical suspension eye in the blade protection quiver
- Environmentally-friendly and quiet thanks to battery operations, therefore usable also in areas sensitive to noise
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

| Order no.                   | 601717850        |
|-----------------------------|------------------|
| EAN code                    | 4061792204089    |
| Battery voltage             | 18 V             |
| Blade length                | 45 cm / 18 "     |
| Cutting length              | 43 cm / 17 "     |
| Max. cutting thickness      | 19 mm / 3/4 "    |
| Number of strokes (No Load) | 2600 spm         |
| Weight without battery pack | 2 kg / 4.4 lbs   |
| Weight with battery pack    | 2.5 kg / 5.5 lbs |

### Scope of delivery

Blade protection quiver, without battery pack, without charger