



## MA-HS 50

- Cutting of high hedges and shrubs with the hedge trimmer attachment of the Metabo multifunction system, the all-in-one solution for many garden applications
- Together with the cordless multifunction drive MA 36-18 LTX BL Q an environmentally-friendly, quiet system, ideal for areas sensitive to noise
- Metabo "Quick" quick coupling system for tool-free attachment replacement
- Highly efficient, precise dual cutting system thanks to diamond-ground blade teeth on both sides
- Cutter bars can be swivelled by 215° in 13 steps without tools for the optimal angle depending on the working situation
- Trigger guard protects user and gearing when working near walls and the ground
- Robust use thanks to durable metal gear unit
- Easy transport and space-saving storage with folded cutter bar

<b>Order no.</b>	<b>601726850</b>
<b>EAN code</b>	<b>4061792229501</b>

Blade length	50 cm / 19 11/16 "
Cutting length	48 cm / 18 29/32 "
Max. cutting thickness	22 mm / 7/8 "
Cutting angle	0 - 215 °
Number of strokes (No Load)	0 - 2600 / 0 - 3100 rpm
Length	1645 mm / 64 3/4 "
Length with drive	2620 mm / 103 5/32 "
Weight	2.8 kg / 6.2 lbs

### Scope of delivery

Blade protection quiver