



## KHE 2845 Q

- Combination hammer with 3 functions: hammer drilling, drilling and chiselling
- Metabo Quick: quick change between SDS Plus hammer chuck and keyless chuck (accessory) for drilling in wood and metal
- Vario (V)-Electronics for working at customised speeds to suit various application materials
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the drill stop unexpectedly
- Lockable switch for comfortable working in continuous operation

Order no.	601740500
EAN code	4061792227965
Max. single blow energy (EP-TA)	3 J
Maximum impact rate	4400 bpm
Rated input power	880 W
Drill-Ø concrete with hammer drills	28 mm / 1 3/32 "
Drill-Ø masonry with core bits	82 mm / 3 7/32 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	30 mm / 1 3/16 "
No-load speed	0 - 1200 rpm
Speed at rated load	830 rpm
Bit retainer	SDS-plus
Collar diameter	50 mm / 2 1/16 "
Weight (without power cable)	3.1 kg / 6.83 lbs
Cable length	4 m / 13 ft

### Scope of delivery

Hammer chuck for tools with SDS-plus shank end, rubber-coated side handle, Drilling depth guide, Plastic carry case