



CS 24-355 S

- Powerful metal chop saw for powerful, fast cutting of profiles, pipes and rods made of steel, NF metals, iron and cast profiles
- Quick clamping device with variable mitre setting for angled cuts from -15° to 45°
- Large handle transversal to the cutting axis for optimum power transmission while cutting
- Adjustable cutting depth limiter for optimum use of the cutting disc
- Electronic soft start for smooth start-up and reduced start-up current
- Easy, fast disc change with spindle lock
- Maximum user safety: swivelling cutting guard, adjustable spark deflector sheet and rubberised base for safe cutting
- Safety switch for protection against accidental start up
- Robust, large machine table with practical storage for hexagonal wrenches
- Easy to transport due to built-in handle and locking device

Order no.	601787000
EAN code	4061792211841
Grinding wheels (Ø x bore)	355 x 25.4 mm // 13 31/32 x 1 "
No-load speed	3700 rpm
Rated input power	2400 W
Max. cutting capacity round tube	132 mm / 5 3/16 "
Max. cutting capacity square tube	120 x 120 mm // 4 23/32 x 4 23/32 "
Max. cutting capacity rectangular tube	100 x 208 mm // 3 15/16 x 8 3/16 "
Max. cutting capacity L-profile	150 x 150 mm // 5 29/32 x 5 29/32 "
Dimensions of the base plate	456 x 256 mm // 17 15/16 x 10 1/16 "
Transport height	394 mm / 15 1/2 "
Weight	16.8 kg / 37 lbs
Cable length	4 m / 13 ft

Scope of delivery

Hexagonal wrench, Inner support flange, Flange nut, Cutting disc 355 mm