



KS 18 LTX 57

- Powerful, light, cordless circular saw for universal use on construction sites
- Aluminium base plate can be directly used on guide rails from Metabo and Mafell, Bosch, Festool, Makita, HiKOKI, Hilti and other manufacturers
- Fast brake stops the saw blade quickly and improves safety
- Accurately angled bevel cuts down to 50°, with handy snap-in point at 45°
- 0° position re-adjustable for highest cutting precision
- Clearly visible cutting indicator for precise sawing after initial cut
- Handle with non-slip soft-grip surface for safe guidance
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	601857840
EAN code	4007430327345
Battery voltage	18 V
Swivel range from / to:	± 0 / + 50 °
Adjustable cutting depth	0 - 57 mm // 0 - 2 1/4 "
Maximum cutting depth at 90°	57 mm / 2 1/4 "
Maximum cutting depth at 45°	43 mm / 1 11/16 "
Max. cutting depth with guide rail	52 mm / 2 1/16 "
Saw blade Ø x bore	165 x 20 mm // 6 1/2 x 5/8 "
No-load speed	4600 rpm
Max. cutting speed	40 m/s / 129 ft/min
Weight without battery pack	2.8 kg / 6.2 lbs
Weight with battery pack	3.2 kg / 7.1 lbs

Scope of delivery

Carbide circular saw blade (18 teeth), Parallel guide, Hexagonal wrench, metaBOX 340, without battery pack, without charger