



ASA 25 L PC with Manual Filter Cleaning

- Compact vacuum cleaner for liquids and dry solids with commercial registration
- Ideal for mobile use due to low weight and compact construction
- For extraction from power tools and to clean construction sites, workshops etc.
- Power socket for a power tool for using the automatical-start-up/shut-down of the vacuum cleaner
- PressClean: manual filter cleaning using strong air flow by activating the switch on the extraction unit during breaks
- User protection: certified in accordance with EU standard for L class dust
- Automatic shut-down when vacuuming liquids once the maximum fill level is reached
- With integrated blow function for blowing out, drying and drawing off exhaust air
- Cable and hose bracket for practical transport
- Practical accessory case and storage area

Order no.	602014000
EAN code	4007430246677
Air output max.	3600 l/min / 127 cfm
Vacuum	210 hPa (mbar) / 3 psi
Filter surface	3000 cm ² / 465 sq.inch
Input power max.	1250 W
Container volume	25 l / 7 gal
Suction hose Ø	32 mm / 1 1/4 "
Hose length	3.5 m / 11 ft
Weight	8.3 kg / 18.3 lbs
Cable length	7.5 m / 25 ft

Scope of delivery

Suction hose (Ø 32 mm / 3.5 m), Handle adapter, 2 Aluminium suction pipes, Pleated polyester filter, PE Filter bags, Fleece filter bag, Crevice nozzle, Floor nozzle (300 mm wide), Suction nozzle (120 mm wide), Brush nozzle, Cable/hose bracket