



## AS 18 L PC Compact with manual filter cleaning

- Portable, compact cordless vacuum cleaner for wet and dry vacuum cleaning (IPX4), ideal for smaller cleaning and extraction jobs
- User safety: certified in accordance with EU standard for dust class L
- PressClean: manual filter cleaning using strong air flow by activating the switch on the extraction unit during breaks
- Eco mode for longer runtime per battery pack charge, boost mode for maximum power
- With integrated blow function for blowing out, drying and drawing off exhaust air
- With stretchy hose for comfortable handling and maximum freedom of movement when vacuuming
- Dust-proof and splash-proof battery pack compartment with lockable flap
- Hoses, pipes and nozzles can be stored directly on the vacuum cleaner
- Easy transport with ergonomically-designed handle or carry strap
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

Order no.	602028850
EAN code	4061792197534

Battery voltage	18 V
Air output max.	2100 l/min
Vacuum	120 hPa (mbar)
Filter surface	3000 cm <sup>2</sup>
Container volume	6 l
Suction hose Ø	32 mm
Hose length	2.5 m
Weight without battery pack	3.8 kg
Weight with battery pack	4.8 kg

### Scope of delivery

Stretchy suction hose (Ø 32 mm / 0.5-2.5 m), 3 Plastic suction tubes, Intermediate sleeve, Fleece filter bag, Suction nozzle (120 mm wide), Crevice nozzle, Carrying strap, Coupling bush internal Ø 28 mm / external Ø 35 mm