



PowerMaxx SRA 12 BL with 80 x 133 mm base plate

- Extremely light, handy cordless orbital sander of the 12 Volt class, ideal for effective grinding of small areas.
- Comfortable guidance close to the surface thanks to the low overall height.
- Low-vibration working thanks to smooth running operation
- Grip area with non-slip soft-grip surface
- Unique Metabo brushless motor highest efficiency when grinding, also in continuous mode
- Orbit diameter 2.0 mm for highest surface quality with good material removal
- Infinitely variable speed control for working with different materials
- With easy to empty textile dust bag for working without extraction facilities
- Can be connected to an all-purpose vacuum cleaner with the coupling bush 630798000
- Removable protector protects adjacent surfaces and increases the service life of the sanding plate
- For grinding of corners and edges, the triangular grinding plate 635219000 (accessory) can be mounted
- With attachment point for tool safety straps for working at great heights
- With metaBOX, the intelligent solution for transport and storage

Order no.	602036840
EAN code	4061792200890
Battery voltage	12 V
Base plate	80 x 133 mm
No-load speed	4000 - 10000 rpm
Orbital frequency with no load	8000 - 20000 rpm
Orbit diameter	2 mm
Weight without battery pack	1 kg
Weight with battery pack	1.4 kg

Scope of delivery

Base plate 80x133 mm with hook and loop, Protector 80x133 mm, 1 Hook and loop sanding sheet P 120 wood and metal "professional" (80x133 mm), Textile dust bag compact, Hexagonal wrench, metaBOX 215, without battery pack, without charger