



## HG 20-600

- Versatile hot air gun with adjusting wheel for easy, variably adjustment of the temperature
- High-quality ceramic heating, powerful motor and optimum device cooling for long service life
- Wide range of uses: removal of varnish, shaping, crimping, welding and much more
- Ergonomic design and handle with non-slip soft-grip surface provides convenient handling
- Safe stationary application due to large non-slip floor space

Order no. EAN code	602066500 4061792186057
Air volume	150 / 300 / 500 l / min // 5 / 11 / 18 cfm
Number of air volume levels	3
Air temperature	80 - 600 °C // 176 - 1112 °F
Number of air temperature levels	infinitely variable
Input power max.	2000 W
Weight (without power cable)	0.62 kg / 22 oz
Cable length	2.2 m / 7 ft

### Scope of delivery

Wide jet nozzle (50 mm), Wrap around nozzle, Reducing nozzle (9 mm), metaBOX 145