



HO 18 LTX 20-82

- Light, compact cordless planer for planing, rebating and chamfering
- Adjustable planer depth and notch depth
- Aluminium die cast and milled cut planer base with V-groove for easy chamfering
- Parallel guide for precise guiding of the planer
- Grip area with non-slip soft-grip surface
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Angled chip ejection adapter for controlled ejection of the wood shavings
- Easy to empty textile dust bag for working without extraction facilities
- Strap on the planer base for stopping the machine and to protect the work piece
- Easy blade change of the robust reversible carbide planer blades
- Soft start and overload protection for long service life of motor and drive
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	602082890
EAN code	4007430325082
Type of battery pack	Li-Power
Battery voltage	18 V
Planing width	82 mm
Adjustable planing depth	0 - 2 mm
Maximum notch depth	9 mm
No-load speed	16000 rpm
Length of planer base	295 mm
Weight without battery pack	2.9 kg / 6.4 lbs
Weight with battery pack	3.3 kg / 7.3 lbs

Scope of delivery

Reversible carbide planer blades, Parallel Guide, Depth gauge, Chip ejection adapter, Textile dust bags, without battery pack, without charger