



SB 18 LT

- Powerful Metabo 4-pole motor for fast drilling and screwdriving
- High-performance impact mechanism for optimum drilling performance
- Integrated working light to illuminate the contact area
- Handy belt hook, can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	602103840
EAN code	4007430286932
Battery voltage	18 V
Maximum torque - soft	34 Nm / 301 in-lbs
Maximum torque, hard	60 Nm / 531 in-lbs
Adjustable torque	0.7 - 8 Nm // 6 - 71 in-lbs
Drill-Ø masonry	13 mm / 1/2 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	38 mm / 1 1/2 "
No-load speed	0 - 450 / 0 - 1600 rpm
Maximum impact rate	27200 bpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	1.3 kg / 2.9 lbs
Weight with battery pack	1.7 kg / 3.7 lbs

Scope of delivery

Keyless chuck, Belt hook and bit case, metaBOX 145, without battery pack, without charger