



RBE 9-60 Set

- Compact tube belt sander with high belt speeds for productive processing of stainless steel pipes
- Large wrap angle of 190° for smooth surfaces
- Metabo Marathon motor with patented dust protection for long service life
- Thumbwheel controlled Vario-Constamatic (VC)-Full wave electronics ideal for working on materials requiring customised speeds, and at speeds which remain almost constant under load
- Tool-free change of sanding belt and adjustable belt guide
- Electronic overload protection for long service life
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after power supply interruption
- Auto-stop carbon brushes to protect the motor

Order no.	602183510
EAN code	4007430298898
Rated input power	900 W
Output power	470 W
Belt speed in idle	8 - 14 m/s // 1575 - 2756 ft/min
Dimensions of grinding belt	30 x 533 mm // 1 3/16 x 21 "
Maximum pipe diameter	60 mm / 2 3/8 "
Wrap angle	190 °
Weight (without power cable)	3.1 kg / 6.8 lbs
Cable length	4 m / 13 ft

Scope of delivery

10 Sanding belts zirconia (30x533 mm; P80), 2 Pyramid sanding belts (30x533 mm; P280/A65), 2 Pyramid sanding belts (30x533 mm; P400/A45), 2 Pyramid sanding belts (30x533 mm; P600/A30), 2 Pyramid sanding belts (30x533 mm; P1200/A16), 3 Fleece bands (30x533 mm; medium), Metal carry case