



BS 18 LTX Impuls

- Robust drill/screwdriver with maximum power for demanding applications
- Selectable "impuls" mode for removal of stubborn screws and for spot-drilling on smooth surfaces
- Powerful Metabo 4-pole motor for fast drilling and screwdriving
- Overload protection: protects the motor from overheating
- Spindle with hexagonal recess for screwdriver bits for working without chuck
- Collar (Ø 43 mm) for versatile use
- Integrated working light to illuminate the contact area
- Robust die cast aluminium gear housing for optimum heat dissipation and long service life
- Handy belt hook, can be fixed either on the right or left side
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	602191890
EAN code	4007430238917
Battery voltage	18 V
Maximum torque - soft	55 Nm / 487 in-lbs
Pulse torque	60 Nm / 531 in-lbs
Maximum torque, hard	110 Nm / 974 in-lbs
Adjustable torque	1.5 - 24 Nm // 13 - 221 in-lbs
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	65 mm / 2 1/2 "
No-load speeds	0 - 500 / 0 - 1700 rpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	1.7 kg / 3.7 lbs
Weight with battery pack	2.1 kg / 4.6 lbs

Scope of delivery

Futuro Plus keyless chuck with metal sleeve, Side handle, Belt hook, without battery pack, without charger