



## RF 80 D

- For testing and inflating tyres
- Ergonomic composite housing: insulated non-slip and low vibration for comfortable work
- Easy operation with precision gauge, overpressure safe
- Handle with non-slip soft-grip surface
- With torque plug
- Large Ø 80mm pressure gauge for good readability
- Digital, illuminated pressure gauge for highest accuracy
- Switchable display units: PSI, BAR, Kpa, kg/cm<sup>2</sup>
- Pressure gauge with rubber shroud to protect against damage

Order no.	602236000
EAN code	4007430241030

Operating pressure	0.5 - 12 bar // 7.3 - 174 psi
--------------------	-------------------------------

Hose length	100 cm / 3 ft
-------------	---------------

Weight	0.55 kg / 1.2 lbs
--------	-------------------

### Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4"