



AG 18

- Lightweight cordless blower e.g. for blowing off chips from workpieces, workplace, transporter etc.
- Good ergonomics provided by a rubberised handle and an optimum centre of gravity
- Robust design suitable for applications in the workshop and on the construction site
- Vario (V)-Electronics for continuously selectable blowing air velocity rate
- Thumbwheel for preselection of 3 air velocity rate settings for varied output
- Rubberised end piece of the blow tube to protect delicate surfaces
- Comfortable blowing of floor areas using the supplied extension of the blow tube
- Operation with all Li-Power and LiHD slide-on 18 Volt battery packs
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	602242850
EAN code	4007430286901
Battery voltage	18 V
Air volume	1 / 1.55 / 2.6 m ³ /min // 31 / 54 / 91 cfm
Max. air velocity	74 m/s / 166 mph
Weight without battery pack	1.4 kg / 3.1 lbs
Weight with battery pack	1.8 kg / 4 lbs

Scope of delivery

without battery pack, without charger