



MARATHON
MOTOR



RBE 15-180 Set

- Powerful tube belt sander for processing even larger stainless steel pipes
- Large wrap angle of 270° for smooth surfaces and quick work progress
- Metabo Marathon motor with patented dust protection for long service life
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics with Thumbwheel: for working at customised speeds to suit the application material and speeds that remain almost constant, even under load
- Rubberised drive roller: reduces slipping of the sanding belt
- Tool-free change of sanding belt and adjustable belt guide
- Overload protection: protects the motor from overheating
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after power supply interruption
- Auto-stop carbon brushes to protect the motor

Order no.	602243500
EAN code	4007430298799
Rated input power	1550 W
Output power	940 W
Belt speed in idle	8.4 - 28 m/s // 1650 - 5500 ft/min
Dimensions of grinding belt	40 x 760 mm // 1 1/2 x 30 "
Maximum pipe diameter	180 mm / 7.1 "
Wrap angle	270 °
Weight (without power cable)	3.4 kg / 7.5 lbs
Cable length	4 m / 13 ft

Scope of delivery

Side handle, 10 Sanding belts zirconia (40x760 mm; P80), 2 Pyramid sanding belts (40x760 mm; P280/A65), 2 Pyramid sanding belts (40x760 mm; P400/A45), 2 Pyramid sanding belts (40x760 mm; P600/A30), 2 Pyramid sanding belts (40x760 mm; P1200/A16), 3 Fleece bands (40x760 mm medium), Metal carry case