



BS 18 LT BL Q

- Brushless drill/screwdriver with optimal power for demanding applications
- Metabo Quick System: quick change of bit retainer and bits, for flexible working
- Unique Metabo brushless motor for quick work progress and highest efficiency when drilling and screwdriving
- Integrated working light to illuminate the contact area
- Handy belt hook and bit holder can be fixed either on the right or left side
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	602334890
EAN code	4007430302335
Battery voltage	18 V
Maximum torque - soft	34 Nm / 301 in-lbs
Maximum torque, hard	75 Nm / 663.8 in-lbs
Adjustable torque	0.7 - 8 Nm // 6 - 71 in-lbs
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	38 mm / 1 1/2 "
No-load speeds	0 - 600 / 0 - 2100 rpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	1.3 kg / 2.9 lbs
Weight with battery pack	1.7 kg / 3.7 lbs

Scope of delivery

Quick-change chuck, Quick-change bit holder, Belt hook and bit case, without battery pack, without charger