



W 18 7-125

- Robust angle grinder with powerful motor and slim design for universal applications
- Overload protection: protects the motor from overheating
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after battery pack change
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	602371850
EAN code	4061792230187
Battery voltage	18 V
Disc-Ø	125 mm / 5 "
Max. cutting depth	27 mm / 1 1/16 "
No-load speed	8500 rpm
Spindle thread	M 14
Handle circumference	191 mm / 7 1/2 "
Weight without battery pack	1.6 kg
Weight with battery pack	2.2 kg

Scope of delivery

Guard, Inner support flange, Nut with two holes, Side handle, Flat-pin spanners, without battery pack, without charger