



BRUSHLESS
MOTOR



W 18 L BL 9-115

- Service-free Brushless motor with highest efficiency and maximum handiness
- Slim design for low-fatigue working
- Tool-free adjustable guard; twist-proof
- Electronic safety shutdown: reduces kickback if the disc stops unexpectedly - for high user safety
- Overload protection: protects the motor from overheating
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after battery pack change
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	602373850
EAN code	4061792230385
Battery voltage	18 V
Disc-Ø	115 mm / 4 1/2 "
Max. cutting depth	27 mm
No-load speed	10000 rpm
Spindle thread	M 14
Handle circumference	183 mm / 7.205 "
Weight without battery pack	1.5 kg
Weight with battery pack	2.2 kg

Scope of delivery

Guard, Inner support flange, Nut with two holes, Side handle, Flat-pin spanners, without battery pack, without charger