



SSD 18 LTX 200 BL

- Compact cordless impact driver with 1/4" hexagon recess and 200 Nm, versatile application
- Unique Metabo brushless motor for quick work progress and highest efficiency for any application
- Automatic Power Shift (APS) supports working with self-tapping screws: automatic torque reduction after drilling to prevent overtightening.
- Twelve speed/torque levels for a wide range of applications
- Integrated work light for illumination of the work area
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Handy belt hook, can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	602396840
EAN code	4007430330147
Battery voltage	18 V
Max. screw size	M16
Max. no-load speed	2900 rpm
Maximum impact rate	4000 bpm
Maximum torque	200 Nm / 150 ft. lbs
Speed/torque levels	12
Bit retainer	Hexagon recess 1/4" (6.35 mm)
Weight without battery pack	0.94 kg / 2.1 lbs
Weight with battery pack	1.3 kg / 2.9 lbs

Scope of delivery

Belt Hook, metaBOX 145, without battery pack, without charger