



SSD 18 LT 200 BL

- Compact cordless impact driver with 1/4" hexagon socket and 200 Nm
- Unique Metabo brushless motor for quick work progress and highest efficiency for any application
- Three speed/torque levels for a varied range of applications
- Integrated work light for illumination of the work area
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Handy belt hook, can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage

| Order no. | 602397840 |
|-----------------------------|----------------------------------|
| EAN code | 4061792217232 |
| Battery voltage | 18 V |
| Max. screw size | M16 |
| Max. no-load speed | 3050 rpm |
| Maximum impact rate | 3750 bpm |
| Maximum torque | 200 Nm |
| Speed/torque levels | 3 |
| Bit retainer | Hexagon recess 1/4" (6.35 mm) |
| Weight without battery pack | 1.17 kg / 2.6 lbs |
| Weight with battery pack | 1.57 kg / 3.5 lbs |

Scope of delivery

Belt Hook, metaBOX 145, without battery pack, without charger