



## SSW 18 LT 300 BL

- Compact cordless impact driver with 1/2" male square and 300 Nm
- Unique Metabo brushless motor for quick work progress and highest efficiency for any application
- Three speed/torque levels for a varied range of applications
- Integrated work light for illumination of the work area
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Handy belt hook, can be fixed either on the right or left side
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

Order no.	602398850
EAN code	4061792217263
Battery voltage	18 V
Max. screw size	M16
Max. no-load speed	3050 rpm
Maximum impact rate	3900 bpm
Maximum torque	300 Nm / 220 ft. lbs
Max. loosening torque	480 Nm / 355 ft. lbs
Speed/torque levels	3
Bit retainer	Male square 1/2" (12.70 mm)
Weight without battery pack	1.18 kg / 2.6 lbs
Weight with battery pack	1.58 kg / 3.5 lbs

### Scope of delivery

Belt Hook, without battery pack, without charger