



SSW 18 LTX 800 BL

- Powerful cordless impact driver with 1/2" male square and 800 Nm
- Unique Metabo brushless motor for quick work progress and highest efficiency for any application
- Loosening in APS mode (automatic power shift): prevents falling of the screw/nut with automatic speed reduction after loosening
- Screwdriving in APS mode (automatic power shift): prevents overtightening of the screw/nut with automatic shutdown after the first impact
- High torque accompanied by an exceptionally compact design
- Very powerful for demanding applications
- Low kick-back operation with extremely high torque
- Twelve speed/torque levels for a wide range of applications
- Integrated work light for illumination of the work area
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Handy belt hook, can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	602403840
EAN code	4061792228726
Battery voltage	18 V
Max. screw size	M24
Max. no-load speed	0 - 2575 rpm
Maximum impact rate	3300 bpm
Maximum torque	800 Nm / 590 ft. lbs
Max. loosening torque	1200 Nm / 885 ft. lbs
Speed/torque levels	12
Bit retainer	Male square 1/2" (12.70 mm)
Weight without battery pack	1.95 kg
Weight with battery pack	2.6 kg

Scope of delivery

Belt Hook, metaBOX 145 L, without battery pack, without charger