



HO 26-82

- Light, compact universal planer for planing, rebating and chamfering
- Adjustable planer depth and notch depth
- Aluminium die cast and milled cut planer base with V-groove for easy chamfering
- Parallel guide for precise guiding of the planer
- Grip area with non-slip soft-grip surface
- Extraction possibility by means of connecting an all-purpose vacuum cleaner
- Angled chip ejection adapter for controlled ejection of the wood shavings
- Easy to empty textile dust bag for working without extraction facilities
- Strap on the planer base for stopping the machine and to protect the work piece
- Easy blade change of the robust reversible carbide planer blades

Order no.	602682000
EAN code	4007430321435
Planing width	82 mm / 3.2 "
Adjustable planing depth	0 - 2.6 mm // 0 - 0.1 "
Maximum notch depth	9 mm
No-load speed	17000 rpm
Rated input power	620 W
Output power	360 W
Speed at rated load	11200 rpm
Length of planer base	295 mm / 11.6 "
Weight (without power cable)	2.7 kg
Cable length	4 m

Scope of delivery

1 Set of disposable planer blades, Parallel Guide, Depth gauge, Extraction connector, Chip ejection adapter, Textile dust bags, Hexagonal wrench