



HGE 23-650 LCD

- Precise hot air gun with LCD display for precise setting of temperature and air volume for different materials and applications
- Settings programmable to be retrieved for frequently recurring applications
- High-quality ceramic heating, powerful motor and optimum device cooling for long service life
- Wide range of uses: removal of varnish, shaping, crimping, welding and much more
- LCD temperature display for material-matched working
- Ergonomic design and handle with non-slip soft-grip surface provides convenient handling
- Safe stationary application due to large non-slip floor space

Order no. EAN code	603065500 4061792186095
Air volume	150 / 500 l/min // 5 / 18 cfm
Number of air volume levels	infinitely variable
Air temperature	80 - 650 °C // 176 - 1200 °F
Number of air temperature levels	infinitely variable
Input power max.	2300 W
Weight (without power cable)	0.7 kg / 24.2 oz
Cable length	4 m / 13 ft

Scope of delivery

Wide jet nozzle (50 mm), Wrap around nozzle, Reducing nozzle (9 mm), metaBOX 145