



BS 18 LTX-3 BL Q I Metal

- Brushless 3-speed drill/screwdriver with maximum power: ideal for demanding metal applications
- Extremely powerful chuck with re-tensioning function against slipping of the bit and high degree of concentricity
- Third speed setting with high torque (max. 4,000/min) for extended range of application and even faster drilling progress, especially in metal
- Metabo Quick System: quick change of bit retainer and bits, for flexible working with maximum load
- Selectable "impuls" mode for removal of stubborn screws and for spot-drilling on smooth surfaces
- Precision Stop: electronic torque control with increased precision for accurate and intricate working
- Overload protection: protects the motor from overheating
- Electronic safety shutdown: no kickback if the drill bit stops unexpectedly - for high user safety
- Integrated LED work light with night light function for optimal brightness in the work area
- Handy belt hook and bit holder can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	603180840
EAN code	4061792211650
Battery voltage	18 V
Maximum torque - soft	65 Nm / 575.3 in-lbs
Maximum torque, hard	130 Nm / 1150.6 in-lbs
Adjustable torque	1 - 18 Nm // 8.9 - 159.3 in-lbs
Drill Ø steel	16 mm / 5/8 "
Drill-Ø soft wood	68 mm / 2.68 "
No-load speeds	0 - 450 / 0 - 2000 / 0 - 4000 rpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	2 kg / 4.4 lbs
Weight with battery pack	3 kg / 6.6 lbs

Scope of delivery

Futuro Top quick-change chuck "QuickPlus", Side handle, C-wrench, metaBOX 145 L, without battery pack, without charger