



W 750-115

- Robust, universal and economical: ergonomic angle grinder for any application
- Robust motor
- Twist-proof guard
- Restart protection after power interruption

Order no.	603604000
EAN code	4061792153295
Disc-Ø	115 mm // 4 1/2 "
Rated input power	750 W
Output power	475 W
No-load speed	11500 rpm
Speed at rated load	7000 rpm
Torque	1.9 Nm / 16.8 in-lbs
Spindle thread	M 14
Handle circumference	180 mm / 7.094 "
Weight (without power cable)	1.8 kg / 4 lbs
Cable length	2.5 m / 8.2 ft

Scope of delivery

Guard, Inner support flange, Nut with two holes, Side handle, Flat-pin spanners