



W 750-125

- Robust, universal and economical: ergonomic angle grinder for any application
- Robust motor
- Twist-proof guard
- Restart protection after power interruption

| Order no. | 603605000 |
|------------------------------|----------------------|
| EAN code | 4061792153448 |
| Disc-Ø | 125 mm // 5 " |
| Rated input power | 750 W |
| Output power | 475 W |
| No-load speed | 11500 rpm |
| Speed at rated load | 7000 rpm |
| Torque | 1.9 Nm / 16.8 in-lbs |
| Spindle thread | M 14 |
| Handle circumference | 180 mm / 7.094 " |
| Weight (without power cable) | 1.8 kg / 4 lbs |
| Cable length | 2.5 m / 8.2 ft |

Scope of delivery

Guard, Inner support flange, Nut with two holes, Side handle, Flat-pin spanners