



WEV 850-125 with speed control

- Robust, universal and economical: powerful angle grinder for any application
- Powerful motor with good overload capacity
- Thumbwheel controlled Vario-Constamatic (VC)-Full wave electronics ideal for working on materials requiring customised speeds, and at speeds which remain almost constant under load
- Twist-proof guard
- Electronic overload protection, soft start and restart protection
- Auto-stop carbon brushes to protect the motor

Order no.	603611000
EAN code	4007430338129
Disc-Ø	125 mm // 5 "
Rated input power	850 W
Output power	480 W
No-load speed	3000 - 11500 rpm
Speed at rated load	8500 rpm
Torque	2 Nm / 18 in-lbs
Spindle thread	M 14
Handle circumference	179 mm / 7.063 "
Weight (without power cable)	1.9 kg / 4.2 lbs
Cable length	2.5 m / 8 ft

Scope of delivery

Guard, Inner support flange, Nut with two holes, Side handle, Flat-pin spanners