



W 1100-125

- Robust, universal and economical: powerful angle grinder for any application
- Robust, powerful angle grinder for rapid work progress
- Twist-proof guard
- Restart protection after power interruption

Order no.	60361400
EAN code	4007430338303
Disc-Ø	125 mm // 5 "
Rated input power	1100 W
Output power	700 W
No-load speed	12000 rpm
Speed at rated load	7000 rpm
Torque	3.2 Nm / 28.3 in-lbs
Spindle thread	M 14
Handle circumference	194 mm / 7 5/8 "
Weight (without power cable)	2.1 kg / 4.6 lbs
Cable length	2.5 m / 8 ft

Scope of delivery

Guard, Inner support flange, Nut with two holes, Side handle, Flat-pin spanners