



HGS 22-630

- Practical rod shape for a comfortable working position e.g. when performing tasks at ground level
- Versatile hot air gun with adjusting wheel for easy, variably adjustment of the temperature
- High-quality ceramic heating, powerful motor and optimum device cooling for long service life
- High occupational safety thanks to slim, rubberised handle area and safe storage option
- Matching nozzles for removal of varnish, shaping, crimping, welding and much more (accessories)
- Wide range of uses: removal of varnish, shaping, crimping, welding and much more

Order no.	604063500
EAN code	4061792186101
Air volume	150 / 500 l/min // 5 / 18 cfm
Number of air volume levels	2
Air temperature	80 - 630 °C // 176 - 1166 °F
Number of air temperature levels	infinitely variable
Input power max.	2200 W
Weight (without power cable)	0.65 kg / 23 oz
Cable length	3 m / 10 ft

Scope of delivery

Slit nozzle, Welding nozzle, Reducing nozzle (9 mm), metaBOX 145