



DRS 68 Set 1/2"

- Ergonomic fwd/rev switch
- Easy adjustment of direction of rotation at ratchet head
- Compact design
- For all work with screws/bolts: e.g. repairs on cars, steel construction etc.
- Ergonomic, partially rubber-coated housing: cold-insulating, non-slip and low vibration for comfortable work
- Integrated speed control
- Rotatable exhaust guide at the side of the housing.

Order no. EAN code	604119500 4007430228963
Operating pressure	6.2 bar / 90 psi
Air requirement	220 l/min / 8 cfm
Square holder	1/2"
Speed (RPM)	175 rpm
Max. loosening torque	68 Nm / 602 in-lbs
Weight	1.2 kg / 2.6 lbs

Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", 7 Socket spanners (9, 10, 11, 13, 14, 17, 19 mm), Plastic carry case, Oil bottles, Extension 75 mm, Flexible joint