



## DB 10

- Ergonomically shaped, rubber-coated handle for comfortable and low-fatigue operation
- Quick work progress thanks to high torque of 1,800 / min
- Ergonomic fwd/rev switch
- Exhaust guide with handle

<b>Order no.</b>	<b>604120000</b>
<b>EAN code</b>	<b>4007430228956</b>
Operating pressure	6.2 bar / 90 psi
Air requirement	360 l/min / 13 cfm
Speed (RPM)	1800 rpm
Chuck capacity	3 - 10 mm // 1/8 - 3/8 "
Weight	1.2 kg / 2.6 lbs

### Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", Oil bottles