



DS 150 M

- Sturdy and compact machine for sharpening, grinding and deburring tasks
- Low-noise and low-vibration, maintenance-free induction motor
- Motor for single phase alternating current
- Workpiece support adjustable without tools
- Large spark protection guards for eye protection
- Vibration-dampening rubber feet for safe support

Order no.	60415000
EAN code	4061792225961
Grinding wheels (Ø x thickness x bore)	150 x 20 x 20 mm // 5 29/32 x 25/32 x 25/32 "
No-load speed	2980 rpm
Mains voltage	220 - 240 V
Rated input power	370 W
Output power	260 W
Breakdown torque	1.5 Nm / 13.3 ft. lbs
Weight	8.7 kg / 19.2 lbs
Cable length	1.8 m / 70 7/8 "

Scope of delivery

Regular aluminium oxide grinding discs 36 P and 60 N, Spark protection glasses, Work piece support