



AV 18

- High-quality cordless fan for flexible use, independent from mains power
- Battery pack operating time of up to 7 hours (at 5.2 Ah)
- Robust metal cage for maximum air throughput with minimum turbulence
- Adjustable tilting cage for flexible direction of air flow
- Air speed selectable via 3 levels
- Quiet operation even with highest level setting
- Stable tubular frame with rubber feet for safe positioning
- Prepared integrated mounting plate for mounting on a tripod or to the wall
- Operation with all Li-Power and LiHD slide-on 18 Volt battery packs
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	606176850
EAN code	4007430286918
Battery voltage	18 V
Air velocity	1.8 / 2.8 / 3.8 m/s // 4.02 / 6.26 / 8.5 mph
Maximum speed	1300 rpm
Rotor diameter	355 mm / 14 "
Weight without battery pack	1.4 kg / 3.1 lbs
Weight with battery pack	1.8 kg / 4 lbs

Scope of delivery

without battery pack, without charger