



## SSE 1100

- Slim machine with soft-grip handle for comfortable sawing in every working position
- Robust aluminium die-cast gear housing, coated for optimum handling
- Metabo Quick for changing saw blades without tools
- Saw blade rotatable by 180° for working comfortably over-head
- Depth guide can be adjusted without tools for ideal utilisation of the saw blade and diverse applications such as plunge cuts
- Vario (V)-Electronics for working with customised stroke rates for the materials used
- Continuous speed control trigger c/w locking function for continuous operation
- Gear protected against dust and water splashes
- Wide range of uses thanks to the adapted Metabo saw blade range
- Quick sawing progress thanks to powerful motor

<b>Order no.</b>	<b>606177500</b>
<b>EAN code</b>	<b>4007430292971</b>

Rated input power	1100 W
Output power	550 W
Strokes in idle	0 - 2600 rpm
Saw blade stroke	28 mm / 1 3/32 "
Pendulum stroke levels	0
Weight (without power cable)	3.9 kg
Cable length	4 m / 157 1/2 "

### Scope of delivery

Saw blade wood + metal, Plastic carry case