



WE 2200-230

- Robust motor
- Starting current limitation prevents the actuation of the lock on start-up
- Restart protection: prevents unintentional start-up after power supply interruption
- Side handle can be mounted in three positions
- Metabo safety switch prevents unintentional start

Order no.	606437000
EAN code	4007430341433
Disc-Ø	230 mm // 9 "
Rated input power	2200 W
Output power	1520 W
No-load speed	6600 rpm
Speed at rated load	4300 rpm
Torque	13.5 Nm / 120 in-lbs
Spindle thread	M 14
Handle circumference	142 mm / 5.591 "
Weight (without power cable)	5.2 kg / 11.5 lbs
Cable length	4 m / 13 ft

Scope of delivery

Guard, Inner support flange, Nut with two holes, Side handle, Flat-pin spanner