



## WE 24-230 MVT with rotating main handle

- Metabo Marathon motor with patented dust protection for long service life
- Electronic safety shutdown: reduces kickback if the disc stops unexpectedly - for high user safety
- Deadman's switch for high user protection
- Rotating back handle and side handle can be mounted at 3 positions for optimum handle position also when cutting
- Tool-free adjustable guard; twist-proof
- Starting current limitation prevents the actuation of the lock on start-up
- Electronic overload protection and restart protection
- Metabo VibraTech (MVT): integrated damping system and side handle to reduce vibrations in order to protect the user's health
- Metabo safety switch prevents unintentional start
- Auto-stop carbon brushes to protect the motor
- LED signal indicates triggered restart protection or overheating

| Order no.                    | 606469580          |
|------------------------------|--------------------|
| EAN code                     | 4007430268228      |
| Disc-Ø                       | 230 mm // 9 "      |
| Rated input power            | 2400 W             |
| Output power                 | 1600 W             |
| No-load speed                | 6600 rpm           |
| Speed at rated load          | 4600 rpm           |
| Torque                       | 17 Nm / 150 in-lbs |
| Spindle thread               | M 14               |
| Handle circumference         | 144 mm / 5.669 "   |
| Weight (without power cable) | 5.8 kg / 12.8 lbs  |
| Cable length                 | 4 m / 13 ft        |

### Scope of delivery

Guard, Inner support flange, Nut with two holes, Metabo VibraTech (MVT) side handle, Flat-pin spanner, Plastic carry case